



**1 Innovative quick release Easyfit handle** made up of a central hub firmly coupled with the stem by a **dual spoke grip** that can be released from the hub with a simple operation and used as a **ball seat adjustment tool**

**2** Settings for the customisable Labelling System using the LCE module (available as an accessory). The grey protection plug housed on the central hub can be replaced with

the transparent plug and customisable tag holder with the LSE set (available as an accessory). The **customisation lets you identify the valve on the system** according to specific needs

**3 PE seal system with locked carrier** adjustable via the Easyfit quick release handle

**4 Stem** with high surface finish and **double O-Ring and PTFE**

**anti-friction disk** that limits friction to a minimum and grants excellent operating torque

**5** Valve body set for SHE kit installation (available as an accessory) that blocks the closing and opening manoeuvres with a lock

**6** Machined high surface finish ball that guarantees a smooth operation and increased reliability